



Be Right™



Electrodeless Conductivity Sensor, Sanitary Style, Flange, Polypropylene Body Material, 50-ft Cable

Product #: 3705E2T50N

NZD Price (Incl. GST): Contact Hach
Not in stock - ships within 4-6 weeks

Polypropylene, Sanitary (CIP) Flange Mounting Style, 15m (50ft) Analog Cable, Electrodeless Conductivity Sensor

Wide Measuring Range

Hach's Inductive Conductivity Sensors measure 200 up to 2,000,000 microSiemens/cm. A built-in Pt 1000 RTD compensates the measured conductivity for changes in process temperature.

Low Maintenance Design

The inductive sensor design eliminates polarization and electrode coating problems that commonly affect conventional contacting electrode-type conductivity sensors.

Versatile Mounting Styles

Sensors can be installed using a choice of four mounting styles—immersion, insertion, union, and sanitary.

Principal of Operation

Inductive conductivity sensors induce a low current in a closed loop of solution, then measure the magnitude of this current to determine the solution's conductivity. The conductivity analyzer drives Toroid A, inducing an alternating current in the solution. This current signal flows in a closed loop through the sensor bore and surrounding solution. Toroid B senses the magnitude of the induced current which is proportional to the conductance of the solution. The analyzer processes this signal and displays the corresponding reading.

Withstands Harsh Environments

The inductive sensor is available in sanitary (CIP) flange style and convertible styles in PFA®, polypropylene, PEEK®, and PVDF material. Select sensors can withstand high pressures and temperatures.

Specifications

Body material:	Polypropylene
Cable Length:	50
Mounting:	Sanitary

What's in the box?

Includes: sensor with 50 ft cable and manual

Required Accessories

- SC200 Universal Controller: 100-240 V AC with one analog conductivity sensor input and two 4-20 mA outputs (Item LXV404.99.00202)

- SC200 Universal Controller: 100-240 V AC (North America power cord) with two analog conductivity sensor inputs, and five 4-20mA outputs (Item LXV404.99.59222)